

IEC Pin and Sleeve
60A, 550V DC, 2 Pole, 3 Wire



Watertight Receptacle

Features

- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Watertight neoprene gland seal to prevent water ingress from entering at cable entrance
- Sequential contact engagement to prevent a momentary over-voltage



Ordering Information

Description	UPC	Catalog Number
DC Rated Pin and Sleeve Receptacle	783585242361	HBL360R8WDC

Listings

UL Listed, File E146032
 CSA Certified File LR285C

Specifications


Housing	PBT
Closure Covers	PBT
Sealing Gasket	Solid Neoprene
Retainer	High-Impact Thermoset
Gaskets	Santoprene
Terminal Screws	Stainless Steel

Performance

Electrical	
Current Interrupting Abnormal Overload	These devices are not rated for current rupture One cycle of operation making and breaking 150% of rated current
Max. Working Voltage	550V DC

Mechanical	
Impact Resistance	Per UL1682
Product Identification	Identification and ratings are a permanent part of the device housing
Terminal Identification	Terminals identified in accordance with North American and IEC conventions

Environmental	
Flammability	V-0
Ingress Protection	TYPE 3R,3RX,4X and IP68,IP69K
Moisture Resistance	IEC 60309-1
Operating Temperatures	Maximum Continuous 75°C; Minimum - 40°C w/o impact



Complementary Products

Cover Assemblies

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

