

HBL363C6W

By Hubbell Wiring Device-Kellems
Catalog # [HBL363C6W](#)

IEC Pin and Sleeve Female Connector Body 63A Watertight



Features

- Self-closing gasketed cover
- Color coded housings for easy identification
- Super tough insulated non-metallic housing

Application

High Ampacity Connections

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstand 3000V AC, Electrical - Max. Working Voltage - 600V RMS, Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17, Environmental - Ingress Protection - IP67 Suitability, Environmental - Moisture Resistance - Watertight per IEC 60309-1, Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum - 40°C w/o impact, Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682, Mechanical - Product Identification - Ratings are a permanent part of the device housing, Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

Specifications

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified File LR280C • UL Classified to IEC 60309-1 IEC 60309-2 • UL Listed, File E146033
Environmental Conditions	Watertight
EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Range	#8 AWG to #2 AWG
Number Of Wires	3-Wire
Number Of Conductors	3-Wire Grounding
Number Of Poles	2-Pole

Current

Current / Amperage Rating	63 A
Connectivity	Pressure Terminal Screws
Current Rating	63 A
Amperage Rating	63 A
Voltage Rating Description	220-240 VAC
Voltage Rating	220-240 VAC

Dimensions

Display Size	Standard
--------------	----------

General

Item Type	Standard
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Watertight Connector Body
Series	HBL Heavy Duty
Specifications	<ul style="list-style-type: none"> • Cord Clamps - Reinforced Thermoplastic Polyester • Covers - Reinforced Thermoplastic Polyester • Gaskets - Solid Neoprene • Glands - Solid Neoprene • Housing - Zytel® ST801 Nylon
UPC	783585403892
Style	Standard Service
Color	Blue

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	<ul style="list-style-type: none"> • Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	---

Product Assets

[Catalog \[English\]](#)