

## Surge Protective Devices, SPIKESHIELD TVSS Duplex Receptacle with Light, 15A 125V, 5-15R, White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5260WSA](#)

Surge Protective Devices, SPIKESHIELD TVSS Duplex Receptacle with Light, 15A 125V, 5-15R, White



### Features

- Automatic self-grounding staple
- Distinctive surge symbol provides quick identification
- Power-on indicator light verifies that power is available
- Alert alarm sounds when surge protection is no longer functioning

### Application

Decorator Duplex

### Performance

Electrical - Protection Modes - Normal and Common Modes, Electrical - Response Time - Approximately 5 ns, Electrical - Transient Suppression - Peak Energy (10 X 100  $\mu$ s), Peak Current (8 X 20  $\mu$ s), Electrical - Voltage - 120V AC + 10% - 15%, Environmental - Flammability - UL 94V-2, Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified to Specification C22.2 No. 42</li> <li>• Listed to UL Standards 498</li> <li>• UL Listed File E2186</li> </ul>
Nema Rating	5-15R

### Current

Current Rating	15 A
Amperage Rating	15 A
Frequency Rating	60 Hz
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Terminal Screws

Voltage Rating 125 V

### Dimensions

Display Size Standard

### General

Series	Specification Grade
OEM Brand Name	Hubbell Wiring Device-Kellems
Outlet	Straight Blade
Color	White
Item Type	Surge Protection Receptacles
Material - Mounting Hardware	Mounting Screws
Type	Duplex
Material	Composite
Specifications	<ul style="list-style-type: none"> <li>• Base Material - Nylon</li> <li>• Contact Design - Tandem Modified Bypass</li> <li>• Face Material - Nylon</li> <li>• Mounting Strap - .050" (1.3) Steel-Zinc Coated</li> <li>• Power Contact - .031" (.8) Brass</li> </ul>
UPC	783585219905

### Logistics

Carton Quantity 10

### Operational

Response Time	5
Indicator(s) Type	None
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)  
[Installation Manual \[English\]](#)