

**HUBBELL**  
Wiring Device-Kellems

## 4-PLEX, Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, with Surge, Blue

By Hubbell Wiring Device-Kellems  
Catalog # [HBL420HS](#)

4-PLEX, Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, with Surge, Blue

### Features

- Mounts directly to 4-inch square box
- Heavy duty, impact resistant housing
- Removable knockouts for mounting
- Heavy duty, triple wipe, brass power and ground contacts

### Application

4-Plex with LED

### Performance

Electrical - Frequency - 60Hz, Electrical - Protection Modes - Normal and Common Modes, Electrical - Response Time - Approximately 5 ns, Electrical - Transient Suppression - Peak Energy (10 X 100  $\mu$ s), Peak Current (8 X 20  $\mu$ s), Electrical - Voltage - 20V AC + 10% - 15%, Environmental - Flammability - UL 94V-2, Environmental - Operating Temperature - -40°F to 140°F (-40°C to 60°C)

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA 22.2, No. 42 File 285</li><li>• Listed to UL Standard 498 File E2186</li></ul>
Nema Rating	5-20R

### Current

Current Rating	20 A
Amperage Rating	20 A
Frequency Rating	60 Hz
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	20 A
Connectivity	Terminal Screws
Voltage Rating	125 V



### Dimensions

Display Size Standard

### General

Series	Hospital Grade
OEM Brand Name	Hubbell Wiring Device-Kellems
Outlet	Straight Blade
Color	Blue
Item Type	Surge Protection Receptacles
Material - Mounting Hardware	Mounting Screws
Type	4-Plex
Material	Composite
Specifications	<ul style="list-style-type: none"><li>• Base Material - Lexan®</li><li>• Contact Design - Triple Wipe</li><li>• Face Material - Lexan®</li><li>• Mounting Screws - Brass</li><li>• Power Contacts - .032 in. (.8) Brass</li></ul>
UPC	783585017891

### Logistics

Carton Quantity 5

### Operational

Response Time	5
Indicator(s) Type	LED Only
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[Spanish, French, English\]](#)