

Straight Blade Devices, Female Connector Body, Corrosion Resistant, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R

By Hubbell Wiring Device-Kellems

Catalog # [HBL52CM69V](#)

Straight Blade Devices, Female Connector Body, Corrosion Resistant, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Yellow, Single Pack

Features

- Powerful cord grips
- Removable cord inserts
- Unique patented clamp type terminals

Application

Marine Grade

Performance

- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Electrical - Max. Working Voltage - 125V or 250V as rated
- Electrical - Temperature Rise - Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Maximum continuous 75°C
- minimum -40°C (w/o impact)
- Mechanical - Product Identification - Molded Rating on Device Face
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA (Brass, White, Green)

General

Catalog Number	HBL52CM69V
Color	Yellow
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Valise
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Specifications	<ul style="list-style-type: none">• Body Holding Screws - Steel, Multiple Drive



- Contact and Ground Springs - Brass
 - Cord Diameter Range - .22-.66 in. (5.6-16.8)
 - Housing - Nylon
 - Line Terminal Screws - Steel-Copper, Multiple Drive
 - Wire Clamps - Steel
- Maximum Continuous: 75° C;
Minimum Continuous: -40° C
w/o impact, -25° with impact.
783585808291

Temperature Rating

UPC

Dimensions

Display Size Standard

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC

Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number of Conductors	3-Wire Grounding

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK AA-39 Catalog Page](#)

[Catalog Page - WDK AA-37 Catalog Page](#)

[Catalogs - WDK Catalog Full 2024](#)

[Installation Manuals - WIRING_PD1558_INSTALLINST](#)

[Literature - Hubbell Marine Full Line Catalog](#)

[Sales Drawings - WDK_HBL52CM69V_DRAWING_PDF](#)

[Specifications - HBL52CM69V](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-HBL52CM69V-SPEC-EN | REV 3/2025