

Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, Gray, NEMA 4X Enclosure, with Aux Contact AC2

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS3AC2](#)

Switches and Lighting Controls, Industrial Grade, Disconnect
Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw
Terminals, Gray, NEMA 4X Enclosure, with Aux Contact AC2

Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- IP69k and Type 4X,12K water ingress protection
- Certified by NSF for hygiene in food processing applications
- Highly visible red handle which meets OSHA Lockout/Tagout capabilities
- Reversible interior accomodates top or bottom conduit opening

Application

Labelless

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage, Electrical - Dielectric Voltage - Withstands 3000V AC minimum, Electrical - Max. Working Voltage - 600V AC RMS, Environmental - Flammability - UL94-5VA and V0 Classification, Environmental - Operating Temperature - Max Continuous 75°C, Min Continuous -40°C w/o impact, Environmental - UV Resistance - All materials are UV stabilized, Mechanical - Impact Resistance - In accordance with UL 746C, Mechanical - Mounting - Non-Metallic - External fully adjustable feet, Mechanical - Product Identification - Identification and ratings are part of external label, Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Specifications

Industry Standard(s)	UL Listed
EU RoHS Indicator	No

Configuration

Mounting Method	External fully adjustable feet
-----------------	--------------------------------



Current

Dielectric Strength	Withstands 3000V AC minimum
Current / Amperage Rating	30 A
Current Rating	30 A
Amperage Rating	30 A

Dimensions

Width	6 in
Height	4.12 in
Length	8.5 in
Dimensions	8.5 in x 6 in x 4.12 in

General

Type	Disconnect Switches
Enclosure Type	Type 4X, IP69k
Series	Non-Fused
Specifications	<ul style="list-style-type: none">• Base - Valox®• Enclosure Gasket - Neoprene• Handle - Valox®• Shaft (Unfused) - Valox®• Top - Valox®
UPC	783585145440
Style	Heavy Duty

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
-----------------------	--

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)