

## IEC Pin and Sleeve

100 A, 380-415 VAC, 3-Pole, 4-Wire

## Advantage Switch-Rated Connector

# HUBBELL

### Features

- Approved as a disconnecting means for motor circuits and branch circuits
- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights



### Ordering Information

<b>Color</b>	<b>UPC</b>	<b>Catalog Number</b>
Red	783585575315	HBSL4100C6W

### Listings

UL Listed, File E146033  
CSA Certified File LR280C  
UL Classified to IEC 60309-1 IEC 60309-2

### Specifications

Style	IP69k NEMA 4X
Connection	Pressure Screw Terminal
Material	Composite
Enclosure	Non-Metallic Housing, Brass Contacts
Mounting	Cord Mounted
Wire Size	#6AWG - #1AWG
Environmental Conditions	Watertight

### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

### Performance

#### Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstand 3000V AC
Max. Working Voltage	600V RMS

#### Mechanical

Impact Resistance	Per CSA C22.2 No. 182.1 / UL1682
Product Identification	Identification and ratings are a permanent part of the device housing
Terminal Identification	Terminals identified in accordance with North American and IEC conventions

#### Environmental

Flammability	V-0
Ingress Protection	TYPE 3R,3RX,4X AND IP68,IP69K
Moisture Resistance	IEC 60309-1
Operating Temperatures	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

