

Surge Protective Devices, SPIKESHIELD
TVSS Plug Strips, 6) Receptacles, Metallic
Body, 1050 Joules, 6' Cord

By Hubbell Wiring Device-Kellems
Catalog # [HBL6MPS1050](#)

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6)
Receptacles, Metallic Body, 1050 Joules, 6' Cord

Features

- Office White color for aesthetics and metal housing
- 1050 joule rating
- 6 foot cord
- wire management

Application

Standard Devices

Performance

Electrical - Max Surge Current - 19.5kA, Electrical - Max.
Operating Voltage - 130, Electrical - Operating Frequency -
50/60Hz, Environmental - Operating Temperature - -40°F to
160°F (-40°C to 70°C)

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes

Conductor

Cord Length	6 ft
-------------	------

Configuration

Number Of Outlets	6
-------------------	---

Current

Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Plug-In

Dimensions

Display Size	1050 Joules
--------------	-------------

General

Series	Economy Surge Strips
OEM Brand Name	Hubbell Wiring Device-Kellems
Outlet	Straight Blade 5-15R
Color	Office White
Item Type	Surge Protection Plug Strips
Material - Mounting Hardware	Portable
Type	Metallic
Material	Steel
Specifications	• Color - Off. White • Height - 1.5" (38.1) • Housing - Metal • Length - 12.25" (311.2) • Width - 2.5" (63.5)
UPC	783585120676

Logistics

Carton Quantity	20
Pallet Quantity	400

Operational

Response Time	5
Indicator(s) Type	LED Indicator
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)

