

## Field Attachable Micro-Quick Control Connectors, Male Angled 4 Wire, Insulation Displacement

By Hubbell Wiring Device-Kellems  
Catalog # [MIMA14IDC](#)

Field Attachable Micro-Quick Control Connectors, Male Angled 4 Wire, Insulation Displacement

### Features

- Strain relief bushing protects terminations
- Wire Guide for virtually toolless termination
- Insulation displacement contacts are made of Copper Alloy

### Application

Quick Connect/Disconnect Signal and Control

### Specifications

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07</li><li>• UL 2238 and UL50E, File No. E192071</li></ul>
EU RoHS Indicator	Yes

### Conductor

Conductor Type	Copper
Number Of Conductors	4-Pole

### Dimensions

Diameter Live Part	.67"
--------------------	------



### General

OEM Brand Name	Hubbell Wiring Device-Kellems
Specifications	<ul style="list-style-type: none"><li>• Contact Materials - Copper Alloy</li><li>• Contact Plating - Tin over Nickel</li><li>• Housing - Polyester Elastomer, Black</li><li>• Strain Relief Bushing - Neoprene, Black</li><li>• Wire Guide - Nylon 6/6, Gray</li></ul>
UPC	783585226729
Color	Black

### Logistics

Carton Quantity	25
-----------------	----

### Operational

Temperature Rating	-20 Deg C to 105 Deg C
--------------------	------------------------

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[Spanish, French, English\]](#)