

Linkosity Inlet, Hazardous Location, 20A 5-Wire

By Hubbell Wiring Device-Kellems
Catalog # [RM2705PB001](#)



Linkosity Inlet, Hazardous Location, 20A 5-Wire

Features

- Linkosity Inlet
- Hazardous Location
- 20A 5-Wire

Application

Power and Control Integration

Specifications

| | |
|-------------------|----------|
| EU RoHS Indicator | Yes |
| Nema Rating | Non-NEMA |

Conductor

| | |
|----------------------|---------|
| Conductor Type | Copper |
| Number Of Conductors | 5 |
| Number Of Poles | 5-Pole |
| Conductor Size | #12 AWG |

Current

| | |
|---------------------------|-------------|
| Current / Amperage Rating | 20 A |
| Current Rating | 20 A |
| Amperage Rating | 20 A |
| Wattage | 12000 |
| Voltage Rating | 600V Max kV |

General

| | |
|----------------|-------------------------------|
| Item Type | Male Receptacle |
| Construction | Fabricated |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Material | Composite |
| UPC | 783585355832 |
| Color | Gray |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 50 |
|-----------------|----|

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[Spanish, French, English\]](#)