

Surge Protection Device - Surge Protective Device, 7-Mode, 277/480 VAC 3Ph Y, Type 1, Surge Current Rating 100kA

Item H10S13Y2DG1



PRODUCT DESCRIPTION

Intermatic PANELGUARD® Surge Protective Devices are designed to react quickly and eliminate surges providing optimal protection to downstream equipment. PANELGUARD Industrial/Commercial-grade series are Parallel Connected Surge Protective Devices designed to protect all types of loads fed from individual disconnects, sub-panels, distribution panels and service entrance locations.

FEATURES

- ▶ Type 1 surge protection
- ▶ Optional audible alarm and dry relay contacts
- ▶ 7 Modes of protection
- ▶ NEMA 4X enclosure for indoor or outdoor installation
- ▶ Individually integrated disconnect TPMOV surge protection technology
- ▶ Blue LED status indicator per phase, red LED service indicator

APPLICATIONS

- ▶ Distribution Panel
- ▶ Service Entrance

TECHNICAL DATA

General	
Model Number	H10S13Y2DG1
Description	Surge Protective Device, 7-Mode, 277/480 VAC 3Ph Y, Type 1, Surge Current Rating 100kA
UPC Code	078275152113
Brand	Intermatic
Country of Origin (Intermatic)	U.S.A.
Warranty Period	10-Year limited
Electrical Specifications	
Modes of Protection	7
Short Circuit Current Rating	200 kA
Nominal Discharge Current	20 kA
Maximum Surge Current Rating Per Phase	100 kA
Maximum Surge Current Rating Per Mode	50 kA
Surge Protection Technology	Individually integrated thermal disconnect technology TPMOV
Maximum Continuous Operating Voltage (L-G)	320
Maximum Continuous Operating Voltage (L-L)	640
Maximum Continuous Operating Voltage (L-N)	320
Maximum Continuous Operating Voltage (N-G)	320
Voltage Protection Rating (L-G)	1200
Voltage Protection Rating (L-L)	2000
Voltage Protection Rating (L-N)	1200
Voltage Protection Rating (N-G)	1200
Voltage	277/480 VAC 3-Phase Wye

Control Specifications	
Surge Protection Type	1
Surge Protection LED Indicator	Yes

Mechanical Specifications	
Enclosure Type	NEMA Type 4X

Dimensions	
Product Dimensions (H x W x D) in	10.59 x 5.25 x 3.29 in
Wire Lead Length (in)	18"
Wire Size Max	#10 AWG
Conduit Size	3/4"

Material Specifications	
Color	Gray

Diagnostics Monitoring	
Diagnostics Indicator	Blue LED Status Indicator Per Phase; Red LED Service Indicator

Benefits	
Filter	No Filter

Packaging	
Shipping Weight (lbs)	0.6
Unit Carton Dimensions (H x W x L) in	4.375 x 6.375 x 12.625 in
Product Weight (kg)	0.27
Product Weight (lbs)	0.6

Environmental Specifications	
Temperature (operation)	-40 °F to 176 °F / (-40 °C to 80 °C)

Standards and Certifications	
UL Certification	ANSI/UL 1449 4th Edition
CSA Certification	CSA C22.2 No. 269.1-14 (VZCA, VZCA7)
Other Certifications and Compatibilities	2020 National Electric Code, Article 242 (previously NEC, Art. 285), 700.10 & 708.20; ANSI/IEEE C62.72-2016, ANSI/IEEE C62.41.1, C62.41.2-2002; C62.45-2002, ANSI/IEEE C62.62-2010 environments: Categories: A, B & C
California Proposition 65	Lead
RoHS Certification	Yes

DRAWINGS AND DIAGRAMS

