

## Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

# Extra Heavy Duty Hospital Grade SNAPConnect® Receptacle

## Features

- Audible SNAP, indicates solid connection
- Reduces installation time
- Fully insulated design

## Ordering Information

| Description                                               | Device Color | UPC Number   | Catalog Number |
|-----------------------------------------------------------|--------------|--------------|----------------|
| Hospital grade, isolated ground with power indicating LED | Red          | 783585249292 | SNAP2182RIGL   |

## Listings

UL Listed to UL498 File No. E2186  
CSA Certified  
Fed. Spec. W-C-596  
NEMA® WD-6 Compliant


## Specifications

|                                 |                   |
|---------------------------------|-------------------|
| Face                            | Nylon             |
| Base                            | PBT               |
| Power Contacts                  | Brass             |
| Ground Contacts                 | Brass             |
| Mounting Strap                  | Galvanized steel  |
| Automatic Self-grounding Staple | Stainless steel   |
| Mounting Screws                 | Zinc plated steel |

## Performance

| Electrical             |                                                                     |
|------------------------|---------------------------------------------------------------------|
| Current Interrupting   | Receptacle certified for current interrupting at full rated current |
| Dielectric Voltage     | Withstands 2,000V minimum                                           |
| Mechanical             |                                                                     |
| Product Identification | Ratings are a permanent part of the device                          |
| Environmental          |                                                                     |
| Flammability           | UL 94V-2                                                            |
| Operating Temperature  | Maximum continuous 75°C; minimum -40°C (without impact)             |

# HUBBELL



## Complementary Products

Wallplate or Weatherproof Cover

StyleLine® Decorator Opening

## Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

