

## Surge Protection Device - Surge Protective Device, 7-Mode, 347/600 VAC 3Ph Y, Type 1, Audible Alarm, Form C Contact, Surge Current Rating 100kA

Item H10S13Y3DG2



### PRODUCT DESCRIPTION

Intermatic PANELGUARD® Surge Protective Devices are designed to react quickly and eliminate surges providing optimal protection to downstream equipment. PANELGUARD Industrial/Commercial-grade series are Parallel Connected Surge Protective Devices designed to protect all types of loads fed from individual disconnects, sub-panels, distribution panels and service entrance locations.

### FEATURES

- ▶ Type 1 surge protection
- ▶ Optional audible alarm and dry relay contacts
- ▶ 7 Modes of protection
- ▶ NFPA 780, UL 96A Lightning system protection compliant
- ▶ NEMA 4X enclosure for indoor or outdoor installation
- ▶ Individually integrated disconnect TPMOV surge protection technology
- ▶ Blue LED status indicator per phase, red LED service indicator

### APPLICATIONS

- ▶ Distribution Panel
- ▶ Service Entrance

### TECHNICAL DATA

General	
Model Number	H10S13Y3DG2
Description	Surge Protective Device, 7-Mode, 347/600 VAC 3Ph Y, Type 1, Audible Alarm, Form C Contact, Surge Current Rating 100kA
UPC Code	078275152168
Brand	Intermatic
Country of Origin (Intermatic)	U.S.A.
Warranty Period	10-Year limited
Electrical Specifications	
Modes of Protection	7
Short Circuit Current Rating	200 kA
Nominal Discharge Current	20 kA
Maximum Surge Current Rating Per Phase	100 kA
Maximum Surge Current Rating Per Mode	50 kA
Surge Protection Technology	Individually integrated thermal disconnect technology TPMOV
Maximum Continuous Operating Voltage (L-G)	400
Maximum Continuous Operating Voltage (L-L)	800
Maximum Continuous Operating Voltage (L-N)	400
Maximum Continuous Operating Voltage (N-G)	400
Voltage Protection Rating (L-G)	1500
Voltage Protection Rating (L-L)	2500
Voltage Protection Rating (L-N)	1500
Voltage Protection Rating (N-G)	1500
Voltage	347/600 VAC 3-Phase Wye

### Control Specifications

Surge Protection Type	1
Surge Protection LED Indicator	Yes

### Mechanical Specifications

Enclosure Type	NEMA Type 4X
----------------	--------------

### Dimensions

Product Dimensions (H x W x D) in	10.59 x 5.25 x 3.29 in
Wire Lead Length (in)	18"
Wire Size Max	#10 AWG
Conduit Size	3/4"

### Material Specifications

Color	Gray
-------	------

### Diagnostics Monitoring

Diagnostics Indicator	Blue LED Status Indicator Per Phase; Red LED Service Indicator; Audible Alarm Indicator; Form C Dry Relay Contacts
-----------------------	--

### Benefits

Filter	No Filter
--------	-----------

### Packaging

Shipping Weight (lbs)	0.6
Unit Carton Dimensions (H x W x L) in	4.375 x 6.375 x 12.625 in
Product Weight (kg)	0.27
Product Weight (lbs)	0.6

### Environmental Specifications

Temperature (operation)	-40 °F to 176 °F / (-40 °C to 80 °C)
-------------------------	--------------------------------------

### Standards and Certifications

UL Certification	ANSI/UL 1449 4th Edition
CSA Certification	CSA C22.2 No. 269.1-14 (VZCA, VZCA7)
Other Certifications and Compatibilities	2020 National Electric Code, Article 242 (previously NEC, Art. 285), 700.10 & 708.20; ANSI/IEEE C62.72-2016, ANSI/IEEE C62.41.1, C62.41.2-2002; C62.45-2002, ANSI/IEEE C62.62-2010 environments: Categories: A, B & C; NFPA 780 & UL 96A Lightning protection systems
California Proposition 65	Lead
RoHS Certification	Yes

**DRAWINGS AND DIAGRAMS**

