

## Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

# Extra Heavy Duty SNAPconnect® Standard Duplex Receptacles for Controlled Applications

# HUBBELL

## Features

- Permanently marked with universal power symbol and the word "CONTROLLED" to visually identify receptacles used in automatic energy management systems
- Patented TR design eliminates plug-in difficulty and TR complaints
- Markings can be read regardless of mounting orientation
- Complies with NEC Section 406.3, ASHRAE 90.1, and California Title 24 requirements
- Complements Hubbell's Load Logic control system or other available energy management system



## Ordering Information

| Description                                    | Device Color | UPC Number   | Catalog Number     |
|--|--------------|--------------|--------------------|
| SNAPconnect® Standard Duplex Smooth nylon face | Ivory        | 783585583167 | SNAP5262C1ITR<br>A |

## Listings

UL Listed to UL498 File No. E2186  
Certified to CSA, C22.2, No. 42 File 285  
Fed. Spec. W-C-596  
NEMA® WD-6 Compliant

## Online Resources

[eCatalog](#)

## Specifications

|                                 |                   |
|---------------------------------|-------------------|
| Face                            | Nylon             |
| Base                            | PBT               |
| Power Contacts                  | Brass             |
| Ground Contacts                 | Brass             |
| Mounting Strap                  | Galvanized steel  |
| Automatic Self-grounding Staple | Stainless steel   |
| Mounting Screws                 | Zinc plated steel |

## Performance

### Electrical

|                      |  |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage   | Withstands 2,000V minimum                                |

### Mechanical

|                        |  |
|------------------------|--|
| Product Identification | Ratings are a permanent part of the device |
|------------------------|--|

### Environmental

|                       |   |
|-----------------------|---|
| Flammability          | UL 94V-2  |
| Operating Temperature | Maximum continuous 75°C; minimum -40°C (w/o impact) |

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

