

Surge Protection Device - Surge Protective Device, 7-Mode, 120/208 VAC 3Ph Y, Type 1, Surge Current Rating 200kA

Item H20S13Y1DG1



PRODUCT DESCRIPTION

Intermatic PANELGUARD® Surge Protective Devices are designed to react quickly and eliminate surges providing optimal protection to downstream equipment. PANELGUARD Industrial/Commercial-grade series are Parallel Connected Surge Protective Devices designed to protect all types of loads fed from individual disconnects, sub-panels, distribution panels and service entrance locations.

FEATURES

- ▶ Type 1 surge protection
- ▶ Optional audible alarm and dry relay contacts
- ▶ 7 Modes of protection
- ▶ NFPA 780, UL 96A Lightning system protection compliant
- ▶ NEMA 4X enclosure for indoor or outdoor installation
- ▶ Individually integrated disconnect TPMOV surge protection technology
- ▶ Blue LED status indicator per phase, red LED service indicator

APPLICATIONS

- ▶ Distribution Panel
- ▶ Service Entrance

TECHNICAL DATA

General	
Model Number	H20S13Y1DG1
Description	Surge Protective Device, 7-Mode, 120/208 VAC 3Ph Y, Type 1, Surge Current Rating 200kA
UPC Code	078275152236
Brand	Intermatic
Country of Origin (Intermatic)	U.S.A.
Warranty Period	10-Year limited
Electrical Specifications	
Modes of Protection	7
Short Circuit Current Rating	200 kA
Nominal Discharge Current	20 kA
Maximum Surge Current Rating Per Phase	200 kA
Maximum Surge Current Rating Per Mode	100 kA
Surge Protection Technology	Individually integrated thermal disconnect technology TPMOV
Maximum Continuous Operating Voltage (L-G)	150
Maximum Continuous Operating Voltage (L-L)	300
Maximum Continuous Operating Voltage (L-N)	150
Maximum Continuous Operating Voltage (N-G)	150
Voltage Protection Rating (L-G)	700
Voltage Protection Rating (L-L)	1000
Voltage Protection Rating (L-N)	700
Voltage Protection Rating (N-G)	700
Voltage	120/208 VAC 3-Phase Wye

Control Specifications		
Surge Protection Type		1
Surge Protection LED Indicator		Yes

Mechanical Specifications		
Enclosure Type		NEMA Type 4X

Dimensions		
Product Dimensions (H x W x D) in		10.59 x 5.25 x 3.29 in
Wire Lead Length (in)		18"
Wire Size Max		#10 AWG
Conduit Size		3/4"

Material Specifications		
Color		Gray

Diagnostics Monitoring		
Diagnostics Indicator		Blue LED Status Indicator Per Phase; Red LED Service Indicator

Benefits		
Filter		No Filter

Packaging		
Shipping Weight (lbs)		0.6
Unit Carton Dimensions (H x W x L) in		4.375 x 6.375 x 12.625 in
Product Weight (kg)		0.27
Product Weight (lbs)		0.6

Environmental Specifications		
Temperature (operation)		-40 °F to 176 °F / (-40 °C to 80 °C)

Standards and Certifications		
UL Certification		ANSI/UL 1449 4th Edition
CSA Certification		CSA C22.2 No. 269.1-14 (VZCA, VZCA7)
Other Certifications and Compatibilities		2020 National Electric Code, Article 242 (previously NEC, Art. 285), 700.10 & 708.20; ANSI/IEEE C62.72-2016, ANSI/IEEE C62.41.1, C62.41.2-2002; C62.45-2002, ANSI/IEEE C62.62-2010 environments: Categories: A, B & C; NFPA 780 & UL 96A Lightning protection systems
California Proposition 65		Lead
RoHS Certification		Yes

DRAWINGS AND DIAGRAMS

