

## Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

## Hospital Grade SNAPConnect® Receptacle

# HUBBELL

### Features

- Requires minimal box space
- Self-grounding clip makes installation ease
- One-piece nickel-plated brass integral ground strap

### Ordering Information

Description	Device Color	UPC Number	Catalog Number
Standard Duplex	Brown	883778305542	SNAP8300USB

### Listings

UL Listed to UL498 File No. E2560  
Certified to CSA, C22.2, No. 42 File 683  
Fed. Spec. W-C-994  
NEMA® WD-6 Compliant

### Specifications

Face	Nylon
Base	PBT
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Brass
Automatic Self-Grounding Clip	Stainless Steel
Mounting Screws	Zinc plated steel

### Performance

#### Electrical


Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

#### Mechanical

Product Identification	Ratings are a permanent part of the device
------------------------	--

#### Environmental

Flammability	UL 94V-7
Operating Temperature	Maximum continuous 75°C; minimum -40°C (without impact)



### Complementary Products

Wallplate or Weatherproof Cover  
Opening

### Online Resources

Customer Sales Drawing  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

