



STOCK NUMBER	MODEL NUMBER	DESCRIPTION	SAW TYPE	DRIVE TYPE	MOTOR (HP)	MITERING TYPE	MITERING DEGREES	PAGE NUMBER
HORIZONTAL/VERTICAL BANDSAW								
413460	HBS-812G	8 x 12" Horizontal/Vertical Geared Head Bandsaw	Horizontal/Vertical	Geared Head	1 HP, 115/230V, 1Ph	Vise	45°	24
414559	HBVS-712	7" x 12" Horizontal/Vertical Bandsaw	Horizontal/Vertical	Step Pulley	3/4HP, 115/230V, 1-Ph	Vise	45°	25
414560	HBVS-712D	7" x 12" Horizontal/Vertical Bandsaw	Horizontal/Vertical	Step Pulley	3/4HP, 115/230V, 1-Ph	Vise	45°	25
NEW 414548	HVBS-56V	5" x 6" Variable Speed Horizontal/Vertical Bandsaw	Horizontal/Vertical	Variable Speed	1/2 HP, 115V	Vise	45°	29
414458	HVBS-56M	5" x 6" Horizontal/Vertical Bandsaw	Horizontal/Vertical	Step Pulley	1/2 HP, 115V, 1Ph	Vise	45°	30
Manual FERROUS COLD SAWS								
414217K	J-FK350-4K	350mm Ferrous Manual Cold Saw	Ferrous	N/A	2 HP, 460V, 3Ph	Head	45° L & R	34
414214K	J-FK350-2K	350mm Ferrous Manual Cold Saw	Ferrous	N/A	2 HP, 230V, 3Ph	Head	45° L & R	34
414227	CS-315	315mm Ferrous Manual Cold Saw	Ferrous	N/A	2 HP, 230V, 3Ph	Head	45° L & R	35
414229	CS-315-1	315mm Ferrous Manual Cold Saw	Ferrous	N/A	2 HP, 220V, 1Ph	Head	45° L & R	35
414226	CS-275	275mm Ferrous Manual Cold Saw	Ferrous	N/A	1-1/2 HP, 230V, 3Ph	Head	45° L & R	35
414228	CS-275-1	275mm Ferrous Manual Cold Saw	Ferrous	N/A	1-1/2 HP, 115V, 1Ph	Head	45° L & R	35
414220	J-F225	225mm Ferrous Manual Bench Cold Saw	Ferrous	N/A	1 HP, 115V, 1Ph	Head	45° L	37
HIGH SPEED NON-FERROUS COLD SAWS								
414207K	J-CK350-4K	350mm Non-Ferrous High Speed Manual Cold Saw	Non-Ferrous	N/A	2 HP, 460V, 3Ph	Head	45° L & R	36
414203K	J-CK350-2K	350mm Non-Ferrous High Speed Manual Cold Saw	Non-Ferrous	N/A	2 HP, 230V, 3Ph	Head	45° L & R	36
ABRASIVE SAWS								
NEW 414240	AB-12	Abrasive Saw 3PH 230V	Abrasive	N/A	5HP, 230V/460V, 3Ph	Head	45° L & R	38
NEW 414245	AB-14	Abrasive Saw 3PH 230V	Abrasive	N/A	5HP, 230V/460V, 3Ph	Head	45° L & R	38
VERTICAL BANDSAWS								
414470	VBS-3612	36" Vertical Bandsaw	Vertical	Variable Speed Pulley	3 HP, 230/460V, 3Ph	Table	10° L & 45° R	31
414482	VBS-2012	20" Vertical Bandsaw	Vertical	Variable Speed Pulley	2 HP, 230/460V, 3Ph	Table	8° F & B, 12° L & 15° R	31
414485	VBS-1610	16" Vertical Bandsaw	Vertical	Variable Speed Pulley	2 HP, 230/460V, 3Ph	Table	8° F & B, 12° L & 15° R	31
414483	VBS-1408	14" Vertical Bandsaw	Vertical	Variable Speed Pulley	1 HP, 115/230V, 1Ph	Table	8° F & B, 12° L & 15° R	31
VERTICAL METAL/WOOD BANDSAW								
414418	VBS-18MW	18" Metal/Wood Vertical Bandsaw	Metal/Wood Vertical	Step Pulley	3/4 HP, 115/230V, 1Ph	Table	15° L & 45° R	32
414500	J-8201K	14" Metal/Wood Vertical Bandsaw	Metal/Wood Vertical	Step Pulley	1 HP, 115/230V, 1Ph	Table	15° L & 45° R	33
414504C	J-8203K	14" Metal/Wood Vertical Bandsaw	Metal/Wood Vertical	Step Pulley	1 HP, 230/460V, 3Ph	Table	15° L & 45° R	33
414502	J-8201VS	14" Metal/Wood Vertical Variable Speed Bandsaw	Metal/Wood Vertical	Variable Speed Pulley	1 HP, 115/230V, 1Ph	Table	15° L & 45° R	33