





Stainless Steel Piston Safety Drum Pump For 5 Gallon Pails, with Flash Arrester - #07713

Product Images





Short Description

- FM Approved
- Stainless Steel
- For 5 Gallon Pails

Description

This manually operated piston safety drum pump for 5-gallon pails and containers is FM approved and delivers up to 3.5 oz. per stroke, ideal for dispensing of and transferring flammable and combustible liquids in a controlled and safe manner. The safety pump can be used with up to 90 weight oil viscosity. Its body is constructed of stainless steel with PTFE seals, offering superior chemical resistance and a long life.

Included with the pump are threaded adapters to fit a variety of pail spouts. The safety pumps have a maximum reach of 12 inches below the lid of the pail. A flash arrestor keeps contents safe from external flame flashbacks. The bonding and grounding clamps come pre-assembled and provide the means to safely ground the receiving container to avoid a static discharge.

Specifications

Model No	07713
UPC	697841000834
Color	Grey
Material Specifications	Stainless Steel
Dimensions, Exterior	19" H x 9" W x 1.25" D
	482.6mm H x 228.6mm W x 31.75mm D
FM Approval	Yes
OSHA Compliance	Yes
Flame Arrestor, inch	.5
Flame Arrestor, mm	12.7
Flame Arrestor Material	Stainless Steel
Mouth Diameter - inch	.5
Mouth Diameter - mm	12.7
Type	Piston
Action Type	Manual
Max Viscosity (Wt.)	90
Maximum Ambient Temperature, °F	140
Includes	Pump, 2 Pail Spout Adapters, 2x Ground Wires with Clamps, Instruction sheet
Net Weight, lbs	4
Net Weight, kg	1.82