



## 2.5 Gallon Plastic Safety Can, Type I, Stainless Steel Hardware, Red - 14261

### Product Images



## Short Description

---

- Chemical-resistant HDPE cans offer safe storage for flammable corrosives
- Features self-closing cap, pressure-relief mechanism and flame arrester
- Conductive carbon insert
- FM approved

## Description

---

Constructed of high-density polyethylene to stand up to tough acids and corrosives, as well as heat, cans are dent, puncture, and chip resistant. The self-closing cap, pressure-relief mechanism and flame arrester work together to prevent ignition sources from entering, without restricting liquid flow in or out of the can. All cans feature stainless steel hardware and flame arrester for superior chemical resistance. FM approved.

Carbon Insert – A conductive current-carrying carbon insert is embedded into the rib of containers, completing a ground path between the cover assembly and the flame arrester. When used with a grounding strip, this provides proper grounding and prevents the creation of a static arc during filling or pouring.

## Specifications

---

Model No	14261
UPC	697841005723
International Model No.	14261
Pallet Quantity	60
FM Approval	Yes
UL Approval	Yes
OSHA Compliance	Yes
Complies with NFPA Code 30	Yes
Color	Red
Material Specifications	Polyethylene
Dimensions, Exterior	14.25" H x 10.75" Outer Dia. 362mm H x 273mm Outer Dia.
Capacity	2.5 gallon
Liter Capacity	9
Fill/Pour Hole inch	1.45
Fill/Pour Hole mm	37
Net Weight, lbs	4.6
Net Weight, kg	2.1