

15 Gallon, Portable Self-Contained Hughes Eyewash Station, Pressurized - 15GEW

Product Images



Short Description

HUGHES



Justrite Safety Group

- 15 US gallon (56.8 liter) stainless steel pressure vessel with built in carrying handles, provides emergency eye washing for up to 15 minutes
- Pop-off dust covers and push lever operation for ease of use
- Pressure gauge and dual action safety valve prevent over pressurization and allow the user to vent the cylinder for cleaning and maintenance
- Includes ANSI-compliant identification sign on activation lever and inspection tag for recording test and service history
- Use integral 1/2-in (F) NPT connection to attach optional drench hose OPT50 for decontamination of body parts subjected to minor exposure

Description

Cost-effective, ANSI-compliant solution for locations that are unsuitable for fixed installations or those without access to a plumbed-in water supply.

Specifications

Model No	15GEW
Color	Green
UPC	697841269941
Special Price Type	Sale
Capacity	15 gallon
Liter Capacity	56.8
Net Weight, lbs	44
Net Weight, kg	20
Filled Weight, lbs	127
Filled Weight, kg	57.8
Dimensions, Exterior	41.2" H x 15.9" W x 15.9" D 1047mm H x 404mm W x 404mm D
Water Inlet Size NPT	1/2 in (F)
Minimum Operating Pressure	2.1 bar g, 30 PSI
Maximum Operating Pressure	5.5 bar g, 80 PSI
Water Flow Eye/Face Liters/min	1.5
Water Flow Eye/Face US Gal/min	0.4
Material Specifications	Body: Stainless Steel, Eye/facewash diffusers: Chrome plated brass with stainless steel mesh
Operating Valve Material	316L Stainless
Pipework Material	Stainless Steel
Activation Method	Push Plate
Minimum Ambient Temperature, °F	41
Minimum Ambient Temperature, °C	5
Maximum Ambient Temperature, °F	95
Maximum Ambient Temperature, °C	35

Operation Duration, min

15