

40.9" W x 17" D Shelf for 45 Gallon, 30/90 Minute EN Safety Cabinets, Powder Coated Steel - 22631

Product Images



Short Description

- Add function and convenience with additional shelves

Description

Protect workers, reduce fire risks, and improve productivity by storing flammable fuels and chemicals in code-compliant safety cabinets. Designed to meet OSHA and NFPA standards, Sure-Grip® EX cabinets are constructed of sturdy 18-gauge (1-mm) thick double-wall, welded steel with 1-1/2" (38-mm) of insulating air space for fire resistance. High-performance, self-latching doors close easily and securely for maximum protection under fire conditions. Fail-safe closing mechanism ensures three-point stainless steel bullet latching system works every time.

For added security, U-Loc™ handle comes with a cylinder lock and key set or accepts an optional padlock. Haz-Alert™ reflective warning labels are highly visible under fire conditions or during power outages when illuminated with a flashlight.

Patented SpillSlope® galvanized steel shelves direct spills to back and bottom of a leakproof 2" (51-mm) bottom sump. They adjust on 3" (76-mm) centers for versatile storage. Cabinets also feature dual vents with flame arresters, four adjustable self-leveling feet, grounding connector, and trilingual warning label. Durable lead-free epoxy/polyester powder-coat finish provides excellent chemical resistance.

All cabinets are FM approved and come with a ten-year warranty.

Self-closing models also meet NFPA1 and the International Fire Code. They shut and latch automatically when a fusible link melts at 165°F (74°C) under fire conditions. Unique, concealed self-closing mechanism offers obstruction-free access to contents.

- See more at:

http://justrite.wsoldev.com/Products/Safety-Cabinets-and-Containers/Safety-Cabinets-for-Flammables/Portable-Mini-Countertop-and-Compact-Cabinets/890200/?id=459_1157&epiworkspaceactive=true&visitorgroupsByID=#sthash.lEs2slyg.dpuf

Expand storage, add new convenience to existing cabinets, or customize your new cabinet with additional shelves to meet specific workflow needs. Powder-coated steel shelves hold up to 165-lbs (75-kgs) and adjust on 1-1/4-inch (32-mm) increments for versatile storage. Shelves with 1-inch (30-mm) high ledge help prevent small containers from easily sliding off.

Specifications

Model No	22631
UPC	697841165526
International Model No.	22631
Color	Light Gray
Material Specifications	Powder-coated Steel
Load Capacity Compliance	165 lb. (75 kg.) uniformly distributed load (UDL)
Dimensions, Exterior	1.18" H x 41.02" W x 17.3" D 30mm H x 1042mm W x 435mm D
Dimensions, Interior	40.9" W x 17" D 1040mm W x 432mm D
Net Weight, lbs	14.0
Net Weight, kg	6.5