
Holds 36, 2.5-Liter Bottles, 1 Shelf, 2 Doors, Manual Close, Corrosives/Acids Plastic Safety Cabinet, White - 24015

Product Images



Short Description

- Sturdy, smooth construction in an attractive design
- Suitable for highly aggressive liquids—no metal parts to corrode
- Three-point door latch on larger units offer secure closure
- Toe kick on undercounter model allows user to stand closer to counter—less leaning, better ergonomics

Description

Research environments using many different types of chemicals have special storage requirements. Whether using acids, bases or solvents, it is critical that incompatible liquids are segregated to avoid disastrous

explosions or fire. The SDS (Safety Data Sheet) should be reviewed to determine chemical characteristics and recommended storage practices.

Solid polyethylene white acid cabinets have excellent chemical resistance to handle the most corrosive chemicals. A protective, all-welded bottom sump and a clean, sleek design complement any laboratory settings. Fully welded, liquid-tight 2" (51-mm) sump contains accidental spills and makes clean up a snap. Shelf adjusts on 3" (76-mm) center. Door accepts a padlock for security.

Specifications

Model No	24015
UPC	697841134980
International Model No.	24015
Color	white
Material Specifications	Polyethylene
Liter Capacity	Thirty six 2½-Liter Bottles
Number of Doors	2
Door Type	Manual
Number of Shelves	1
Adjustable Shelves	Yes
Dimensions, Exterior	36.75" H x 36" W x 21.75" D 933mm H x 914mm W x 552mm D
Dimensions, Interior	35.5" H x 35.5" W x 20.9" D 902mm H x 902mm W x 530mm D
Height (Inches)	36.75
Width (Inches)	36
Depth	21.75
Net Weight, lbs	160.0
Net Weight, kg	72.6