



2 Drum DrumShed™ With Rolltop Doors, EcoPolyBlend™ - 28675

Product Images



Short Description

- Safe, compliant eco-friendly storage for drums
- Features weather-resistant, robust design of eco-friendly recycled polyethylene
- EPA and SPCC compliant
- Ships fully assembled

Description

EcoPolyBlend™ DrumSheds™ feature a weather resistant, robust design made of eco-friendly 50% recycled polyethylene. Convenient roll top doors allow access from front or rear. Wide door opening of 52" accepts

palletized loads. The leak proof pallet sump meets EPA and SPCC requirements and has removable, durable deck grating for easy clean up of spills. A spacious interior offers ample headroom for adding funnels or pumps. Safety features include grounding capability, integral anchor bolt locations for wind resistance, and molded in lugs which accept padlocks for security. Forliftk pockets front and back make it easy to relocate empty sheds. Ships fully assembled.

Optional [pallet ramp](#) for easy loading.

EPA and SPCC Compliant

(UDL) Uniformly Distributed Load - 1250 Lbs/567 Kgs. per drum, for DrumSheds™ and Pallets

Specifications

Model No	28675
UPC	697841133570
International Model No.	28675
Pallet Quantity	1
Color	Yellow
Material Specifications	Recycled Polyethylene
UL Approval	Yes
UL Environmental Approval	Yes
OSHA Compliance	Yes
EPA Compliance	Yes
SPCC Compliance	Yes
Percent Recycled	50
Sump Capacity - Gallons	67
Sump Capacity - liters	254
Load Bearing Capacity, lbs	2500
Load Bearing Capacity, kg	1134
Dimensions, Exterior	60.75" W x 75.25" H x 58.5" D
	1543mm W x 1911mm H x 1486mm D
Net Weight, lbs	285.3
Net Weight, kg	129.4