

HPLC Poly Manifold With Stainless Steel Quick Disconnect for Safety Disposal Can - 28177

Product Images



Short Description

- Cost-effective
- Enables up to six waste lines to be fed into a single intake fitting
- Complies with OSHA and NFPA Code 30
- For use on round containers

Description

The HPLC (PTFE) Manifold is a cost effective way to enable up to six waste lines (per manifold) from HPLC processes to be fed into a single intake fitting. Manifolds have six 1/4-28 ports and one 3/8" NPT port (with caps for unused ports), and either one quick disconnect in No. 316 stainless steel or polypropylene, or a No. 316 stainless steel stacker connector. The six ports are tapped to accommodate the 1/4-28 threads of the

separately available compression fittings.

Safety container with manifold installed is US OSHA compliant and meets NFPA Code 30. Use on round containers; not for use on oval style can.

Specifications

Model No	28177
UPC	697841121416
International Model No.	28177
Color	Silver/White
Material Specifications	Stainless Steel/Polypropylene
Dimensions, Exterior	4.5" H x 5" W x 7" L
	114mm H x 127mm W x 178mm D x 178mm L
Net Weight, lbs	0.3
Net Weight, kg	0.1