

# IBC Outdoor Shed With Pallet, Forklift Pockets, Rolltop Doors, EcoPolyBlend™ - 28677

## Product Images

---



## Short Description

---

- Reliable spill protection and safe storage for indoor IBCs
- Complies with EPA SPCC regulations and meets fire codes
- Ships fully assembled

## Description

---

Constructed of durable 40% recycled polyethylene, these intermediate bulk container pallets offer excellent chemical resistance. Accepts IBCs up to 48"W x 48"D x 53"H (1219 mm x 1219 mm x 1346 mm). Large leakproof sump exceeds regulations and protects against high volume spills. Sturdy pillar supports accept up to 9000 lb (4082 kg) uniformly distributed load. Removable pillars make for easy sump cleanup. Pallet features forklift pockets for relocation when empty. The lockable rolltop doors offer dual access with a handy reach pole that conveniently stores on the side wall. Ships fully assembled.

EPA, SPCC compliant and meets fire codes.

(UDL) Uniformly Distributed Load - 1250 Lbs/567 Kgs. per drum, for DrumSheds™ and Pallets

Safe allowable uniform distributed load of 9000 lbs (4082 kg) based on a service temperature range of -30°F to 120°F (-39°C to 49°C)

## Specifications

---

Model No	28677
UPC	697841133594
International Model No.	28677
Pallet Quantity	1
Color	Yellow
Material Specifications	Recycled Polyethylene
UL Approval	Yes
UL Environmental Approval	Yes
OSHA Compliance	Yes
EPA Compliance	Yes
SPCC Compliance	Yes
Percent Recycled	40
Sump Capacity - Gallons	372
Sump Capacity - liters	1408
Load Bearing Capacity, lbs	9000
Load Bearing Capacity, kg	4082
Dimensions, Exterior	103.75" H x 60.75" W x 68.5" D 1543mm W x 2635mm H x 1740mm D
Net Weight, lbs	322.3
Net Weight, kg	146.2