

Dispensing Shelf for Drum Management System with Stack Module, EcoPolyBlend™, Black - 28671

Product Images



Short Description

- Shelf accommodates load capacity of 60 lbs. and mounts to Stack Module for dispensing from the upper level
- EcoPolyBlend™ is 100% recycled black polyethylene
- Complies with EPA SPCC regulations and meets fire codes

Description

The Dispensing Shelf has a load capacity of 60 lb (27 kg), and mounts securely to the stack module for

convenient dispensing from the upper level.

The Drum Management System is a space-saving, stackable design that stores up to four 30- and/or 55-gallon (110- and/or 200-L) drums of Class 1B or 1C flammables and combustibles or nonhazardous liquids. 100% molded polyethylene construction provides maximum chemical resistance—preventing corrosion, deterioration and leaks. Molded-in drum lock-channels hold drums in place. The system consists of three parts: a base module, stack module and dispensing shelf — EACH PIECE SOLD SEPARATELY

To be used in conjunction with:

The Base Module holds two drums with a 3060-lb (1388-kg) total load capacity. Easily relocate the base module with a forklift when empty. The 66-gallon (250-L) open-view containment sump makes it easy to spot any spills for a quick cleanup.

The Stack Module holds two additional drums to double the system capacity for a load of 1500 lb (680 kg). When storing both 30- and 55-gallon (110- and 200-L) drums, the smaller drums should be placed on the top of the stack module.

EPA, SPCC compliant and meets fire codes.

Load Bearing Capacity — (UDL) Uniformly distributed Load - 1250lbs. (567 kgs) per drum.

Base module capacity of 3060 Lbs. includes stack module and shelf

Note: When storing different sized drums, always place two smaller drums on top of two larger drums.

Safe allowable uniform distributed load of 60 lbs (27 kg) based on a service temperature range of -30°F to 120°F (-39°C to 49°C)

Specifications

Model No	28671
UPC	697841134997
International Model No.	28671
Pallet Quantity	10
Color	Black
Material Specifications	Recycled Polyethylene
UL Environmental Approval	Yes
Percent Recycled	100
Load Bearing Capacity, lbs	60
Load Bearing Capacity, kg	27
Dimensions, Exterior	19.5" W x 16.5" H x 18.75" D
	495mm H x 419mm W x 476mm D
Net Weight, lbs	12.0
Net Weight, kg	5.4