

Single Cylinder Hand Truck | 16" Pneumatic Wheels - 35010

Product Images



Short Description

- Configured with 16-in (406-mm) steel hub pneumatic wheels with dual ball bearings for easier rolling—less effort required
- Rated at 1000-lb (454-kg) weight capacity
- Holds one larger diameter propane or cryogenic cylinder from 9- to 18-in (229- to 457-mm)
- Exclusive bumper guard edging with steel reinforced vinyl protects your cylinders from damage while providing extra grip

Description

Due to their weight, high-pressure contents, and unwieldy shape, industrial gas cylinders require a specially designed hand truck to minimize accidents and injuries. Constructed of 1-in (25-mm) and 1.25-in (32-mm)

diameter steel tube with continuous welding, these hand trucks provides optimum safety, strength and longevity. Robust, v-shaped cylinder support cradles keep cylinder snug and secure, reducing cylinder rolling common in curved back designs. Two durable 1.5- x 66-in (38-mm x 1676-mm) polypropylene support straps, lab tested to 1138-lb (516-kg), feature steel cinch buckle and hold individual cylinders securely for safe transport.

Heavy-duty, 11-gauge (3-mm) floor plate with safety fins prevent warping or breaking. Features unique zero-lift height loading, allowing floor plate to lay flat, thereby eliminating the need to lift cylinder during loading and unloading. Corrosion-resistant powder-coat finish throughout for long life and smooth handling. Upper handle sections bolt in place for reduced package size in order to save on freight costs.

Helps comply with OSHA, NFP1, NFPA 55, and CGA.

Specifications

Model No	35010
UPC	697841209602
Cylinder Capacity	1
Minimum Cylinder Diam (in)	9
Cylinder Capacity with Max Cylinder Dia	(1) 18 inch
Main Wheel Type	Pneumatic
Main Wheel Size (inch)	16
Main Wheel Size (mm)	406
Weight Capacity (lb)	1000
Weight Capacity (kg)	454
Strap Style	Poly Cinch Strap with Steel Buckle
Straps Per Cylinder	2
Material Specifications	Steel
Complies with NFPA 1 Fire-Code	Yes
NFPA 55	Yes
OSHA Compliance	Yes
CGA	Yes
Net Weight, lbs	88
Net Weight, kg	40
Net Dimensions (W x D x H)	36 x 32 x 49 inches
	914 x 813 x 1245 mm