

## Drum Funnel for Non-Flammables, EcoPolyBlend™, Black - 28680

### Product Images

---



### Short Description

---

- An eco-friendly, cost-effective way to collect liquids and keep drum tops clean
- Fits closed head 30 and 55-gallon drums
- 100% recycled content, Black

## Description

---

Use these funnels with any closed-head 30- and 55-gallon (110- and 200-L) drums. Low-profile, wide diameter opening makes it for quick, easy pouring. Scalloped, sloped design minimizes splashes and prevents containers from resting in their own liquids. Large, flat well at the throat of funnel allows for passive draining of paint tins, filters, buckets and other containers.

Funnel for flammable liquids includes a drum fill vent with brass flame arrester, threaded bung cap with tight seal, and pressure relief valve for high temperatures. Molded-in hook stores optional funnel cover.

## Specifications

---

Model No	28680
UPC	697841134560
International Model No.	28680
Color	Black
Material Specifications	Recycled Polyethylene
UL Environmental Approval	Yes
OSHA Compliance	Yes
Percent Recycled	100
Sump Capacity - Gallons	2.5
Sump Capacity - liters	9
Dimensions, Exterior	3.25" H x 21" Outer Dia. 83mm H x 533mm Outer Dia.
Net Weight, lbs	4.0
Net Weight, kg	1.8