

# Single Cylinder Hand Truck With Hoist Ring, 10.5" Pneumatic Wheels - 35016

## Product Images

---



## Short Description

---

- Locking posts and collar plates ensure total cylinder immobilization
- Configured with 10.5-in (267-mm) steel hub pneumatic wheels with dual ball bearings for easier rolling—less effort required
- Rated at 300-lb (136-kg) weight capacity

## Description

---

Move gas cylinders easily around a construction site, into locations with poor accessibility, or from floor to

floor with these hoist-equipped hand trucks. Designed for one cylinder up to 12-in (305-mm) in diameter. Fully welded construction using 1.25-in (32-mm) diameter round steel tube, these durable cylinder hand trucks provide optimum safety, strength, and longevity. Floor plate made of thick 11-gauge (3-mm) steel with safety fins prevents warping or breaking. Extensive structural framing with 0.375-in (10-mm) thick hoist plates make these units safe when lifted by hoist rigs. Triple grip handle design helps user control the high center of gravity by expanding available grip area for improved leverage and swing radius. The zero-lift height loading allows floor plate to lay flat, thereby eliminating the need to lift cylinder during loading and unloading. Corrosion-resistant powder-coat finish throughout for long life and smooth handling.

Two heavy-duty 1.5- x 54-in (38-mm x 1372-mm) polypropylene support straps, lab tested to 1138-lb (516-kg), feature steel cinch buckles for secure attachment of cylinder—eliminate any cylinder rolling potential seen in chain-secured units. Exclusive bumper guard edging grips cylinder and minimizes damage to cylinder and hand truck. Triple grip handle design helps user control the high center of gravity by expanding available grip area for improved leverage and swing radius.

Accessorize hand trucks with a tool tray or lockable tool box for securing equipment.

Developed for the US Navy for use on submarines.

Helps comply with OSHA, NFP1, NFPA 55, and CGA.

## Specifications

---

Model No	35016
UPC	697841209633
Cylinder Capacity	1
Minimum Cylinder Diam (in)	6
Cylinder Capacity with Max Cylinder Dia	(1) 12 inch
Hoist Ring Equipped	Yes
Locking Post Equipped	Yes
Main Wheel Type	Pneumatic
Main Wheel Size (inch)	10.5
Main Wheel Size (mm)	267
Weight Capacity (lb)	300
Weight Capacity (kg)	136
Strap Style	Poly Cinch Strap with Steel Buckle and Chain
Straps Per Cylinder	2
Material Specifications	Steel
Complies with NFPA 1 Fire-Code	Yes
NFPA 55	Yes
OSHA Compliance	Yes
CGA	Yes
Net Weight, lbs	79
Net Weight, kg	36
Net Dimensions (W x D x H)	21 x 19 x 70 inches
	533 x 483 x 1778 mm