

Double Cylinder Hand Truck With Hoist Ring, 16" Pneumatic Wheels - 35034

Product Images



Short Description

- Locking posts and collar plates ensure total cylinder immobilization
- Configured with 16-in (406-mm) steel hub pneumatic wheels with dual ball bearings for easier rolling—less effort required
- Rated at 600-lb (136-kg) weight capacity

Description

Move gas cylinders easily around a construction site, into locations with poor accessibility, or from floor to floor with these hoist-equipped hand trucks. Designed for a pair of cylinders (usually oxy-acetylene) common in welding applications, up to 13-in (330-mm) and 10-in (254-mm) in diameter, respectively. Fully welded construction using 1.25-in (32-mm) diameter round steel tube, these durable cylinder hand trucks provide

optimum safety, strength, and longevity. Floor plate made of thick 11-gauge (3-mm) steel with safety fins prevents warping or breaking. Extensive structural framing with 0.375-in (10-mm) thick hoist plates make these units safe when lifted by hoist rigs. Triple grip handle design helps user control the high center of gravity by expanding available grip area for improved leverage and swing radius. The zero-lift height loading allows floor plate to lay flat, thereby eliminating the need to lift cylinder during loading and unloading. Caster carriage features heavy steel bars and nylon washers for smooth folding action and easy storage in tight spaces. Corrosion-resistant powder-coat finish throughout for long life and smooth handling.

Two heavy-duty 1.5- x 54-in (38-mm x 1372-mm) polypropylene support straps, lab tested to 1138-lb (516-kg), feature steel cinch buckles for secure attachment of cylinder—eliminate any cylinder rolling potential seen in chain-secured units. Exclusive bumper guard edging grips cylinder and minimizes damage to cylinder and hand truck. Triple grip handle design helps user control the high center of gravity by expanding available grip area for improved leverage and swing radius.

Accessorize hand trucks with a tool tray or lockable tool box for securing torches and other equipment.

Developed for the US Navy for use on submarines.

Helps comply with OSHA, NFP1, NFPA 55, and CGA.

Specifications

Model No	35034
UPC	697841210004
Cylinder Capacity	2
Minimum Cylinder Diam (in)	5
Cylinder Capacity with Max Cylinder Dia	(1) 10 inch and (1) 13 inch
Hoist Ring Equipped	Yes
Locking Post Equipped	Yes
Main Wheel Type	Pneumatic
Main Wheel Size (inch)	16
Main Wheel Size (mm)	406
Weight Capacity (lb)	600
Weight Capacity (kg)	272
Strap Style	Poly Cinch Strap with Steel Buckle and Chain
Straps Per Cylinder	2
Material Specifications	Steel
Complies with NFPA 1 Fire-Code	Yes
NFPA 55	Yes
OSHA Compliance	Yes
CGA	Yes
Net Weight, lbs	107
Net Weight, kg	49
Net Dimensions (W x D x H)	35 x 26 x 69 inches
	889 x 660 x 1753 mm