


1 Wide by 2 Deep, Gas Cylinder Barricade Rack, 2 Cylinder Capacity - 35084

Product Images



Short Description

- 12" wide cylinder bays
- Meets USGS high-hazard seismic zone requirements when properly mounted

Description

Recommended for indoor or outdoor bulk cylinder storage, barricade racks surround cylinders with 2-in (51-mm) square steel structural tubing, continuously seam welded at all junction points and sealed with exterior grade powder-coat paint for long lasting strength, durability and dependability. Tops ground smooth and capped with high-density polyethylene (HDPE) caps to prevent corrosion and injuries. Features two levels of

welded steel chains for each cylinder and clasps to connect the chains to the rack, ensuring a snug fit. Pre-drilled 0.531-in (14-mm) diameter floor mounting holes included on lower tube structure. For seismic installations, add Model 35350 S4-rated anchor bolts (not included).

Helps comply with OSHA, NFP1, NFPA 55, and CGA.

Specifications

| | |
|---|---------------------|
| Model No | 35084 |
| UPC | 697841210158 |
| Cylinder Capacity | 2 |
| Minimum Cylinder Diam (in) | 8 |
| Cylinder Capacity with Max Cylinder Dia | (2) 12 inch |
| Mount Type | Floor |
| Mount Holes | 4 |
| Mount Hole Size (inch) | 0.531 |
| Strap Style | Chain |
| Straps Per Cylinder | 2 |
| Material Specifications | Steel |
| Complies with NFPA 1 Fire-Code | Yes |
| NFPA 55 | Yes |
| OSHA Compliance | Yes |
| CGA | Yes |
| High Hazard Seismic Zone | Yes |
| Net Weight, lbs | 82 |
| Net Weight, kg | 37 |
| Net Dimensions (W x D x H) | 16 x 26 x 30 inches |
| | 406 x 660 x 762 mm |