

Stainless Steel Piston Pump For 30 And 55 Gallon Drums, with Flash Arrester - #07717

Product Images





Short Description

- FM Approved
- Stainless Steel
- For 30 and 55 Gallon Drums

Description

Because small quantity dispensing or controlled transferring of flammable liquids from 30 and 55 gallon drums is no easy task, this manually operated, stainless steel piston drum pump can help. It is FM approved and delivers up to 8 oz. per stroke, ideal for transferring flammable and combustible liquids in a controlled and safe manner. The pump can be used with up to 90 weight oil viscosity at 70F. Its body is constructed of stainless steel with PTFE seals, offering superior chemical resistance and a long life.

Included with the pump is a standard two-inch NPT threaded bung adapter and pick-up tube that allows the drum pump to reach up to 36 inches below the lid of the drum. A flash arrestor keeps contents safe from external flame flashbacks. The bonding and grounding clamps come pre-assembled and provide the means to safely ground the receiving container to avoid a static discharge.

Specifications

Model No	07717
UPC	697841270688
Color	Grey
Material Specifications	Stainless Steel
Dimensions, Exterior	46" H x 9" W x 1.25" D
	1168.4mm H x 228.6mm W x 31.75mm D
FM Approval	Yes
OSHA Compliance	Yes
Flame Arrestor, inch	.5
Flame Arrestor, mm	12.7
Flame Arrestor Material	Stainless Steel
Mouth Diameter - inch	.5
Mouth Diameter - mm	12.7
Type	Piston
Action Type	Manual
Max Viscosity (Wt.)	90
Maximum Ambient Temperature, °F	140
Includes	Pump, Pick-Up Tube, 2" NPT Bung Adapter, Grounding Wires with Clamps, Instructions Sheet
Net Weight, lbs	5
Net Weight, kg	2.27