

End Loaded Gas Cylinder Pallet, 6 Cylinder Capacity, with Ramp, Steel - 35212

Product Images



Short Description

- Fully enclosed 7.75-in wide (197-mm) forklift channels with two way access
- Textured finish on the pallet provides a non-skid surface

Description

Transport multiple gas cylinders securely with a forklift using these end-load oriented pallets. Secure a group of gas cylinders using the 10,000-lb (4,536-kg) DOT compliant strap that attaches to frame at either 12-, 24- or 36-in (305-, 610- or 915-mm) from the deck. Fully welded construction from 11-gauge (3-mm) hot-rolled steel and structural tube steel, powder-coated to ensure longevity and chemical resistance. For easier loading and unloading, the pallets includes a 16-in (406-mm) hinged ramp. Once loaded, ramp lifts up to lie flat against unit for compact storage. Helps comply with OSHA, NFP1, NFPA 55, and CGA.

Specifications

Model No	35212
UPC	697841210691
Cylinder Capacity	Varies
Cylinder Capacity with Max Cylinder Dia	(6) 9 inch, (4) 12 inch, or (1) 21 inch
Ramp Equipped	Yes
Mount Type	Forklift
Weight Capacity (lb)	2400
Weight Capacity (kg)	1089
Strap Style	Ratchet Binding
Straps Per Cylinder	1 Total
Material Specifications	Steel
Complies with NFPA 1 Fire-Code	Yes
NFPA 55	Yes
OSHA Compliance	Yes
CGA	Yes
Net Weight, lbs	171
Net Weight, kg	78
Net Dimensions (W x D x H)	24 x 54 x 38 inches
	610 x 1372 x 965 mm