

Gas Cylinder Barricade Rack, 6 Cylinder Capacity, With Ramp, Steel - 35224

Product Images



Short Description

- Secure cylinders up to 10-in (254-mm) in diameter
- Fully enclosed 7.75-in wide (197-mm) forklift channels with two way access

Description

Transport multiple gas cylinders securely with a forklift using these end-load oriented barricade rack pallets. Barricade racks surround cylinders with structural steel tubing, continuously seam welded at all junction points and mounted to the pallet. They are sealed with exterior grade powder-coat paint for long lasting strength, durability and dependability. Tops ground smooth and capped with high-density polyethylene (HDPE) caps to prevent corrosion and injuries. Features two levels of welded steel chains for each cylinder and clasps to connect the chains to the rack, ensuring a snug fit.

Helps comply with OSHA, NFP1, NFPA 55, and CGA.

Specifications

Model No	35224
UPC	697841210752
Cylinder Capacity	6
Minimum Cylinder Diam (in)	6
Cylinder Capacity with Max Cylinder Dia	(6) 10 inch
Mount Type	Forklift
Weight Capacity (lb)	1800
Weight Capacity (kg)	816
Strap Style	Chain
Straps Per Cylinder	2
Material Specifications	Steel
Complies with NFPA 1 Fire-Code	Yes
NFPA 55	Yes
OSHA Compliance	Yes
CGA	Yes
Net Weight, lbs	230
Net Weight, kg	104
Net Dimensions (W x D x H)	24 x 54 x 37 inches
	610 x 1372 x 940 mm