

Low Profile Gas Cylinder Pallet, 4 Cylinder Capacity, Steel - 35230

Product Images



Short Description

- Fully enclosed 7.75-in wide (197-mm) forklift channels with two way access
- Low profile design employs a lower deck—makes cylinder loading and unloading easier
- Exclusive bumper guard edging with steel reinforced vinyl protects your cylinders from damage while providing extra grip
- Accepts cylinders from 4- to 12-in (102- to 305-mm) in diameter

Description

Transport multiple gas cylinders securely with a forklift using these pallets. Fully welded construction from 11-gauge (3-mm) hot-rolled steel, powder-coated to ensure longevity and chemical resistance. Heavy-duty polypropylene support straps, 1.5- x 54-in (38-mm x 1372-mm) and rated at 1138-lb (516-kg), feature steel

cinch buckle and hold individual cylinders securely against integral bracket. Back-to-back cylinder storage offers maximum space utilization. For an improved level of safety for any installation, all brackets include openings to retrofit secondary support chains, one set for each cylinder strap location.

Helps comply with OSHA, NFP1, NFPA 55, and CGA.

Specifications

Model No	35230
UPC	697841210783
Cylinder Capacity	4
Minimum Cylinder Diam (in)	4
Cylinder Capacity with Max Cylinder Dia	(4) 12 inch
Mount Type	Forklift
Weight Capacity (lb)	1200
Weight Capacity (kg)	544
Strap Style	Poly Cinch Strap with Steel Buckle
Straps Per Cylinder	2
Material Specifications	Steel
Complies with NFPA 1 Fire-Code	Yes
NFPA 55	Yes
OSHA Compliance	Yes
CGA	Yes
Net Weight, lbs	130
Net Weight, kg	59
Net Dimensions (W x D x H)	39 x 24 x 32 inches
	991 x 610 x 813 mm