
Gas Cylinder Pallet With Firewall, 12 Cylinder Capacity, Steel - 35222

Product Images



Short Description

- Steel encased Marinite® It creates a one-hour fire barrier between the fuel and oxidizer—exceeds minimum NFPA 55, OSHA and CGA standards
- Fully enclosed 7.75-in wide (197-mm) forklift channels with two way access
- Textured finish on the pallet provides a non-skid surface

Description

Transport multiple gas cylinders securely with a forklift using these end-load oriented pallets. Secure a group of gas cylinders using the two included 10,000-lb (4,536-kg) DOT compliant straps that attaches to frame at either 12-, 24- or 36-in (305-, 610- or 915-mm) from the deck. Fully welded construction from 11-gauge (3-mm) hot-rolled steel and structural tube steel, powder-coated to ensure longevity and chemical resistance.

†Marinite® I is a registered trademark of BNZ Materials, Inc.

Specifications

Model No	35222
UPC	697841210745
Cylinder Capacity	Varies
Cylinder Capacity with Max Cylinder Dia	(12) 9 inch, (6) 12 inch, or (2) 21 inch
Firewall Rating	One-Hour
Mount Type	Forklift
Weight Capacity (lb)	4000
Weight Capacity (kg)	1814
Strap Style	Ratchet Binding - 1 Per Side
Straps Per Cylinder	1 Total
Material Specifications	Steel/Marinite® I
Complies with NFPA 1 Fire-Code	Yes
NFPA 55	Yes
OSHA Compliance	Yes
CGA	Yes
Net Weight, lbs	384
Net Weight, kg	174
Net Dimensions (W x D x H)	32 x 48 x 78 inches
	813 x 1219 x 1981 mm