
Steel Gas Cylinder Stand, 1 Cylinder Capacity, Low Profile - 35282

Product Images



Short Description

- Fully welded construction using 11-gauge (3-mm) steel provides structural integrity and longevity
- Low profile design accepts cylinders from 4- to 10-in (102- to 254-mm) in diameter

Description

Designed for the safe storage of industrial and commercial use compressed gas cylinders, these storage stands help prevent dangerous tipping situations. Powder-coated to ensure long service life and chemical resistance. Features a 0.187-in (5-mm) thick steel clamping bar protected with an edge bumper guard that attaches to the stand using dual threaded rods and wing nuts. Pre-drilled holes in base for floor mounting with application specific fasteners (not included).

Heavy-duty polypropylene support strap, 1.5- x 54-in (38-mm x 1372-mm) and rated at 1138-lb (516-kg), features steel cinch buckle and hold individual cylinders securely against stand.

Helps comply with OSHA, NFP1, NFPA 55, and CGA.

Specifications

Model No	35282
UPC	697841210974
Cylinder Capacity	1
Minimum Cylinder Diam (in)	4
Cylinder Capacity with Max Cylinder Dia	(1) 10 inch
Mount Type	Floor
Mount Holes	3
Mount Hole Size (inch)	0.406
Strap Style	Poly Cinch Strap with Steel Buckle and Clamping Bar
Straps Per Cylinder	1
Material Specifications	Steel
Complies with NFPA 1 Fire-Code	Yes
NFPA 55	Yes
OSHA Compliance	Yes
CGA	Yes
Net Weight, lbs	21
Net Weight, kg	10
Net Dimensions (W x D x H)	16 x 16 x 15 inches
	406 x 406 x 381 mm