

Steel Gas Cylinder Mobile Stand, 1 Cylinder Capacity - 35286

Product Images



Short Description

- Locking collar and post system adds vise-like holding capability to immobilize the cylinder— use of safety cylinder caps ensures DOT compliance
- Heavy-duty 1.5- x 54-in (38-mm x 1372-mm) polypropylene support straps, rated at 1138-lb (516-kg), feature steel cinch buckle and hold individual cylinders securely to prevent tipping
- Exclusive bumper guard edging with steel reinforced vinyl protects your cylinders from damage while providing extra grip

Description

Suitable for over-the-road gas cylinder transportation, these mobile stands accommodate cylinders from 4- to 10-in (102- to 254-mm). Fully welded construction using 11-gauge (3-mm) steel provides structural integrity while the powder-coating provides chemical resistance for a long service life. Locking post extends up to 66-in (1677-mm) in height. Pre-drilled holes in base designed for required floor mounting with application specific fasteners (not included).

For an improved level of safety on any installation, mobile stands include openings to retrofit secondary support chains, one for each strap. Order model 35366 to get optional chain(s).

Helps comply with OSHA, NFP1, NFPA 55, and CGA.

Specifications

Model No	35286
UPC	697841211889
Cylinder Capacity	1
Minimum Cylinder Diam (in)	4
Cylinder Capacity with Max Cylinder Dia	(1) 10 inch
Locking Post Equipped	Yes
Mount Type	Floor
Mount Holes	4
Mount Hole Size (inch)	0.406
Strap Style	Poly Cinch Strap with Steel Buckle
Straps Per Cylinder	2
Material Specifications	Steel
Complies with NFPA 1 Fire-Code	Yes
NFPA 55	Yes
OSHA Compliance	Yes
CGA	Yes
Net Weight, lbs	39
Net Weight, kg	18
Net Dimensions (W x D x H)	16.25 x 10.5 x 41 inches
	413 x 267 x 1041 mm