

Steel Gas Cylinder Storage Stand, 1 Cylinder Capacity - 35278

Product Images



Short Description

- Fully welded construction using 11-gauge (3-mm) steel provides structural integrity and longevity
- Exclusive bumper guard edging with steel reinforced vinyl protects your cylinders from damage while providing extra grip
- Accepts cylinders from 4- to 12-in (102- to 305-mm) in diameter

Description

Designed for the safe storage of industrial and commercial use compressed gas cylinders, these storage stands help prevent dangerous tipping situations. Powder-coated to ensure long service life and chemical resistance. Pre-drilled holes in base for floor mounting with application specific fasteners (not included).

Two heavy-duty polypropylene support straps, 1.5- x 54-in (38-mm x 1372-mm) and rated at 1138-lb (516-kg), feature steel cinch buckle and hold individual cylinders securely against integral bracket. For an improved level of safety for any installation, all brackets include openings to retrofit secondary support chains, one set for each cylinder strap location.

Helps comply with OSHA, NFP1, NFPA 55, and CGA.

Specifications

| | |
|---|------------------------------------|
| Model No | 35278 |
| UPC | 697841210950 |
| Cylinder Capacity | 1 |
| Minimum Cylinder Diam (in) | 4 |
| Cylinder Capacity with Max Cylinder Dia | (1) 12 inch |
| Mount Type | Floor |
| Mount Holes | 4 |
| Mount Hole Size (inch) | 0.406 |
| Strap Style | Poly Cinch Strap with Steel Buckle |
| Straps Per Cylinder | 2 |
| Material Specifications | Steel |
| Complies with NFPA 1 Fire-Code | Yes |
| NFPA 55 | Yes |
| OSHA Compliance | Yes |
| CGA | Yes |
| Net Weight, lbs | 33 |
| Net Weight, kg | 15 |
| Net Dimensions (W x D x H) | 18 x 13.75 x 30 inches |
| | 457 x 349 x 762 mm |