
One-Hour Fire Barrier, 1 Cylinder Deep - 35352

Product Images



Short Description

- Protect workers
- Reduce fire risks
- One-hour fire barrier
- Pre-drilled with mounting holes
- Can be used on exterior walls or free-standing walls

Description

For applications where both fuels and oxidizers are stored in close proximity, a one-hour fire barrier between barricade racks, mounting brackets, or stands exceeds minimum NFPA 55, OSHA and CGA standards for separation of oxidizers and flammable gases. Constructed using fire-resistant Marinite[®] It fully encased into welded steel panels, these units may be mounted to exterior walls and floor using provided mounting holes

with self-supplied fasteners, or be used as a free-standing wall. Lift hook plates supplied for installation positioning.

†Marinite® I is a registered trademark of BNZ Materials, Inc.

Specifications

Model No	35352
UPC	697841211223
Firewall Rating	One-Hour
Mount Type	Wall/Floor
Mount Holes	6
Mount Hole Size (inch)	0.0406
Material Specifications	Steel/Marinite® I
Complies with NFPA 1 Fire-Code	Yes
NFPA 55	Yes
CGA	Yes
Net Weight, lbs	100
Net Weight, kg	45
Net Dimensions (W x D x H)	12 x 2 x 60 inches
	305 x 51 x 1524 mm