


# 17 Gallon, 1 Shelf, 2 Doors, Self Close, Hazardous Material Cabinet, ChemCor® Piggyback, Royal Blue - 8617282

## Product Images



## Short Description

---

- Expand storage and safely segregate hazardous materials
- POWDER-COAT PAINT FINISH PROVIDES INCREASED CHEMICAL RESISTANCE
- Provide complete protection from harsh acids and corrosive chemicals
- Self-closing doors
- Seam-free surface eliminates the need for rivets or fasteners
- Complies with NFPA 1, NFPA 400 and the International Fire Code
- FM-approved

## Description

---

Designed to mount on top of our standard 30- and 45-gallon (114- and 170-L) safety cabinets, these Piggyback cabinets create a safe storage space without taking up any valuable floor space. Cabinets can also be used independently as a wall-mount unit or on a countertop.

ChemCor® thermoplastic coating on all interior surfaces provides superior protection against corrosion from drips and off-gassing from harsh chemicals. Seam-free surface eliminates the need for rivets or fasteners which risk corrosion from seep-through chemicals. Non-porous surface resists staining and cleans up easily.

ChemCor® Lined Hazardous Material Safety Cabinets have the same quality features found in Justrite's flammable cabinets — including double-wall, 18-gauge (1mm) welded steel construction, 2" (51mm) liquid-tight containment sump, dual vents, adjustable shelves, three-point stainless steel bullet self-latching doors with U•Loc™ padlockable handle and Haz-Alert™ reflective warning labels. An all epoxy baked-on powder-coat finish, inside and out, provides increased chemical resistance. Interior ChemCor® liner ensures complete corrosion resistance and protection. Self-close door(s) shuts and latches automatically when a fusible link melts at 165°F (74°C) under fire conditions. Unique, concealed self-closing mechanism offers obstruction-free access to contents.

Includes a polyethylene work tray which can be secured to cabinet top for a handy work surface.

Exclusive to Justrite, each cabinet comes with a "Hazardous - Keep Fire Away" label, as well as a pack of ten application-specific labels to choose from and apply to the cabinet in order to indicate its contents.

Cabinets comply with NFPA 1, NFPA 400 Hazardous Material Code, and the International Fire Code. Cabinets are FM approved and come with a ten-year warranty.

## Specifications

---

Model No	8617282
UPC	697841154643
International Model No.	86172821
Color	Royal Blue
Material Specifications	18-Gauge Steel
FM Approval	Yes
Complies with International Fire Code	Yes
Complies with NFPA Code 30	Yes
Complies with NFPA 1 Fire-Code	Yes
Complies with NFPA 400	Yes
Capacity	17 gallon
Liter Capacity	64
Number of Doors	2
Door Type	Self-close
Number of Shelves	1
Adjustable Shelves	Yes
Dimensions, Exterior	24" H x 43" W x 18" D
	610mm H x 1092mm W x 457mm D
Dimensions, Interior	19.5" H x 39.5" W x 14.6" D
	495mm H x 1003mm W x 370mm D
Height (Inches)	24
Width (Inches)	43
Depth	18
Net Weight, lbs	129.0
Net Weight, kg	58.5