




12 Gallon, 2 Doors, Manual Close, Corrosives/Acids Safety Cabinet, ChemCor® Piggyback, Blue - 8913022

Product Images



Short Description

- Expand storage and safely segregate corrosives
- Provide complete protection from harsh acids and corrosive chemicals
- Fire-protection and code compliance
- 100% seamless thermoplastic coating protects interior surfaces from corrosion
- FM-approved

Description

Research environments using many different types of chemicals have special storage requirements. Whether using acids, bases or solvents, it is critical that incompatible liquids are segregated to avoid disastrous explosions or fire. The SDS (Safety Data Sheet) should be reviewed to determine chemical characteristics and recommended storage practices.

Designed to mount on top of our standard 30- and 45-gallon (114- and 170-L) safety cabinets, these Piggyback cabinets create a safe storage space without taking up any valuable floor space. Cabinets can also be used independently as a wall-mount unit or on a countertop.

The ChemCor® thermoplastic coating on all interior surfaces provides superior protection against corrosion from drips and off-gassing from harsh chemicals. Non-porous surface resists staining and cleans up easily.

ChemCor® Lined Piggyback Acid Safety Cabinets have the same quality features found in Justrite's flammable cabinets — including double-wall, 18-gauge (1mm) welded steel construction, 2" (51mm) liquid-tight containment sump, dual vents, adjustable shelves, three-point stainless steel bullet self-latching doors with U•Loc™ padlockable handle and Haz-Alert™ reflective warning labels. An all epoxy baked-on powder-coat finish, inside and out, provides increased chemical resistance. Interior ChemCor® liner ensures complete corrosion resistance and protection. Manual-close door(s) opens to a full 180 degrees and self-latches when pushed closed.

Manual close models meet OSHA and NFPA 30. Cabinets are FM approved and come with a ten-year warranty.

Specifications

Model No	8913022
UPC	697841112469
International Model No.	89130221
Color	Blue
Pallet Quantity	2
Material Specifications	18-Gauge Steel
FM Approval	Yes
OSHA Compliance	Yes
Complies with NFPA Code 30	Yes
Capacity	12 gallon
Liter Capacity	45
Number of Doors	2
Door Type	Manual
Adjustable Shelves	No
Dimensions, Exterior	18" H x 43" W x 18" D 457mm H x 1092mm W x 457mm D
Dimensions, Interior	13" H x 39.5" W x 14.6" D 330mm H x 1003mm W x 370mm D
Height (Inches)	18
Width (Inches)	43
Depth	18
Net Weight, lbs	108.0
Net Weight, kg	49.0