




15 Gallon, 1 Shelf, 1 Door, Manual Close, Corrosives/Acid Steel Safety Cabinet, Sure-Grip® EX Compac, Blue - 891502

Product Images





Short Description

- Store corrosives safely even when available space is at a minimum
- Offer same quality safety features as cabinets for flammables
- FM-approved
- Ten-year warranty

Description

Research environments using many different types of chemicals have special storage requirements. Whether using acids, bases or solvents, it is critical that incompatible liquids are segregated to avoid disastrous explosions or fire. The SDS (Safety Data Sheet) should be reviewed to determine chemical characteristics and recommended storage practices.

Countertop and Compac Cabinets let you customize your work areas and make the most of available space. Whether adding to existing storage space or making chemicals readily available at workstation locations, these smaller-sized cabinets are the solution when space is at a premium.

Justrite blue steel safety cabinets for corrosives have the same quality safety features as the cabinets for flammables. All models come with double-wall construction, dual vents, grounding wire connections,

adjustable shelves, leakproof sills, three-point self-latching doors and leveling feet. Manual-close door(s) opens to a full 180 degrees and self-latches when pushed closed.

Additionally, they include polyethylene trays attached to galvanized steel shelves and a separate polyethylene liner for the bottom sump resist aggressive chemicals. Easily remove the liner for quick cleaning of drips and leaks. An all epoxy baked-on powder-coat finish, inside and out, provides increased chemical resistance.

Manual close models meet OSHA and NFPA 30. Cabinets are FM approved and come with a ten-year warranty.

Specifications

Model No	891502
UPC	697841112612
International Model No.	8915021
Color	Blue
Pallet Quantity	2
Material Specifications	18-Gauge Steel
FM Approval	Yes
OSHA Compliance	Yes
Complies with NFPA Code 30	Yes
Capacity	15 gallon
Liter Capacity	57
Number of Doors	1
Door Type	Manual
Number of Shelves	1
Adjustable Shelves	Yes
Dimensions, Exterior	44" H x 23.25" W x 18" D
	1118mm H x 591mm W x 457mm D
Dimensions, Interior	39.6" H x 20" W x 14.6" D
	1006mm H x 508mm W x 370mm D
Height (Inches)	44
Width (Inches)	23.25
Depth	18
Net Weight, lbs	120.5
Net Weight, kg	54.7