



# 2-Drum, Explosion Relief Panels, Non-Combustible Outdoor Safety Locker - 911021

## Product Images



## Short Description

---

- Safe and secure hazardous/chemical storage solution
- Explosion relief panels designed to release at 20 psf
- Rugged heavy gauge steel construction
- Meets EPA, NFPA 30 and NFPA 1 requirements; FM-approved
- Customizable with a variety of optional features and accessories

## Description

---

Protect people and the environment and meet insurance requirements by storing hazardous materials in rugged, FM-approved Outdoor Safety Lockers.

Featuring non-combustible construction with heavy gauge steel and built-in secondary containment, every locker is fully compliant to meet EPA 40 CFR, NFPA 30 and NFPA 1 regulations. Proper chemical storage reduces poison hazards and accidents, minimizes contamination of chemicals, and prevents unwanted, costly fines.

Each locker features natural draft ventilation, NFPA 704 diamond decal for content identification, anchoring plates for hold down protection, and multiple static grounding connections for maximum safety. Forklift channels permit easy relocation.

Choose explosion relief panels for the storage of highly volatile Class 1A or dispensing of Class 1A and 1B flammables as defined by NFPA – always check with the local authority having jurisdiction to ensure safety by following all local regulations, including proper setback requirements.

## Specifications

|                                |                                |
|--------------------------------|--------------------------------|
| Model No                       | 911021                         |
| UPC                            | 697841158481                   |
| International Model No.        | 911021                         |
| Color                          | Bone                           |
| Material Specifications        | Steel                          |
| FM Approval                    | Yes                            |
| Complies with NFPA Code 30     | Yes                            |
| Complies with NFPA 1 Fire-Code | Yes                            |
| EPA Compliance                 | Yes                            |
| Dimensions, Exterior           | 77.5" H x 67" W x 62" D        |
|                                | 1969mm H x 1702mm W x 1575mm D |
| Dimensions, Interior           | 55.5" H x 54" W x 30" D        |
|                                | 1410mm H x 1372mm W x 762mm D  |
| 55-Gallon Drum Capacity        | 2                              |
| Base Capacity, lbs             | 2000                           |
| Base Capacity, kg              | 907.2                          |
| Number of Doors                | 1                              |
| Door Type                      | Standard                       |
| Door Hinge                     | Right                          |
| Explosion Relief Panels        | (1) - 48-in x 48-in            |
| Door Height inch               | 51                             |
| Door Width inch                | 42                             |
| Door Height mm                 | 1295                           |
| Door Width mm                  | 1067                           |
| Sump Capacity - Gallons        | 120                            |
| Sump Capacity - liters         | 454                            |

|                                            |       |
|--------------------------------------------|-------|
| Sump Depth - inch                          | 13.5  |
| Sump Depth - mm                            | 343   |
| Storage Capacity cubic feet (Int Volume)   | 52    |
| Storage Capacity cubic meters (Int Volume) | 1.5   |
| Net Weight, lbs                            | 969.0 |
| Net Weight, kg                             | 439.5 |