

# Keg-Mounted, 1 In-Line Nozzle, Hughes Handheld Drench Hose Eyewash Station - OPT50

## Product Images

---



## Short Description

---

# HUGHES



Justrite Safety Group

- Quick installation - 1/2-in NPT (M) connection
- Chrome plated brass valve
- Flexible 34-inch (864-mm) drench hose with cap to keep debris off diffuser

## Description

---

Drench hose for use with 15GEW pressurized, keg-mounted eye/face wash. For decontamination of body parts subjected to minor exposure.

## Specifications

---

Model No	OPT50
Color	Green
UPC	697841269842
Net Weight, lbs	1.5
Net Weight, kg	1
Dimensions, Exterior	44" H x 2.5" W x 3" D
	1118mm H x 64mm W x 76mm D
Water Inlet Size NPT	1/2 in (M)
Water Flow Eye/Face Liters/min	6
Water Flow Eye/Face US Gal/min	1.59
Operating Valve Material	Chrome plated brass
Activation Method	Hand operated lever
Minimum Ambient Temperature, °F	41
Minimum Ambient Temperature, °C	5
Maximum Ambient Temperature, °F	95
Maximum Ambient Temperature, °C	35