

SAUTER AD 0100

Wedge tension clamp 20 kN, steel

KERN



Pictograms

STANDARD



Category

Brand	Sauter
Product category	Clamp
Product group	Wedge Clamp

Construction

Dimension housing (W×D×H)	210×152×40 mm
Dimensions completely mounted (W×D×H)	210×152×40 mm
Material	steel, nickel-plated
Maximum clamp width	40 mm
Clamping width	10 mm
Tensile/compressive force [Max]	20 kN

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Delivery time	14 d
Dimensions packaging (W×D×H)	210×152×40 mm
Shipping method	Parcel service
Net weight approx.	6 kg
Gross weight approx.	6 kg
Shipping weight	5,5 kg

Product information

GTIN/EAN number	4045761174511
Trade number	90278990
REACH classification	no prohibited substances