



55 Gallon, 1 Drum Horizontal, 2 Doors, Manual Close, Flammable Cabinet with Cradle Track, Sure-Grip® EX, Yellow - 899300

Product Images



Short Description

- Use for drum storage or as a dispensing station
- For use in gravity-flow dispensing applications
- FM-approved
- Ten-year warranty

Description

For storage of larger quantities of flammable solvents, the heavy-duty Drum Safety Cabinet is available in many styles and sizes. Built to the same high standards as the smaller Classic Safety Cabinets, a reinforced liquid-tight sump contains spills. An array of drum accessories and equipment is available to ensure safety and convenience when storing and handling drums of hazardous materials.

Safely house horizontal drums for use in gravity-flow dispensing applications. The interior provides space for a drip-can and includes tracks to guide drum cradle (sold separately below) into position. Manual-close doors open to a full 180 degrees and self-latch when pushed closed. Cabinets are FM approved and come with a ten-year warranty.

Specifications

Model No	899300
UPC	697841115163
International Model No.	8993001
Color	Yellow
Pallet Quantity	1
Material Specifications	18-Gauge Steel
FM Approval	Yes
OSHA Compliance	Yes
Complies with NFPA Code 30	Yes
Capacity	55 gallon
Liter Capacity	200
Number of Doors	2
Door Type	Manual
Adjustable Shelves	No
Dimensions, Exterior	50" H x 30" W x 48" D 1270mm H x 762mm W x 1219mm D
Dimensions, Interior	46.4" H x 27" W x 44.8" D 1178mm H x 686mm W x 1137mm D
Height (Inches)	50
Width (Inches)	30
Depth	48
Net Weight, lbs	323.0
Net Weight, kg	146.5