

# SAUTER AD 9 100

**KERN**

Incl. jaws with pyramid grip



## Pictograms

STANDARD



## Category

Brand	Sauter
Product category	Clamp
Product group	Wedge Clamp

## Construction

Dimensions completely mounted (W×D×H)	210×152×40 mm
Material	steel
Mounting - force dissipation	Threaded hole M6 External thread M12
Maximum clamp width	40 mm
Clamping width	10 mm
Tensile/compressive force [Max]	20 kN

## Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

## Packing & Shipping

Delivery time	14 d
Dimensions packaging (W×D×H)	210×152×40 mm
Shipping method	Parcel service
Net weight approx.	6 kg
Gross weight approx.	6 kg
Shipping weight	5,5 kg

## Product information

GTIN/EAN number	4045761178533
Trade number	90278990
REACH classification	no prohibited substances