

KERN KFD 600V40M

KERN

Weighing bridge made from stainless steel, two integrated access ramps, extremely resistant to bending



Category

Brand	KERN
Product category	Component
Product group	Weighing bridge
Product family	KFD-V40-IP68

Measuring System

Weighing capacity [Max]	600 kg
Readability [d]	200 g
Minimum weight [Min]	4 kg
Loadcell type	ZEMIC BM8H 0.5 ton

Construction

Dimensions weighing surface (W×D)	1000×1000 mm
Dimensions weighing surface	1000×1000 mm
Dimensions weighing platform (W×D×H)	1600×1220×95 mm
Material weighing plate	stainless steel
Material platform	stainless steel
Material load cell(s)	stainless steel
Cable length	5 m
Display device cable length	5 m
Allowed cable length display device [Max]	30 m
Platform Construction	Welded load plate; smooth surface
Load cells - number	4

Functions

IP protection - complete device	IP68 (load cell)
IP protection - platform	IP67

IP protection - load cell	IP68
---------------------------	------

Approval

Conformity assessment possible ex works	✓
Verification scale interval [e]	200 g

Services (optional)

Article number for conformity assessment	965-230
Article number for DAkkS calibration	963-130

Packing & Shipping

Delivery time	2 d
Dimensions packaging (W×D×H)	1650×1310×370 mm
Shipping method	Freight
Net weight approx.	130 kg
Gross weight approx.	190 kg
Shipping weight	189 kg

Product information

GTIN/EAN number	404576 1 155787
REACH classification	no prohibited substances

Pictograms

STANDARD



FACTORY

