

6- 16 Drum, 60" Double Door Upgrade, Fire-rated Lockers - 915702

Product Images



Short Description

- For locker applications requiring a larger door
- Includes pallet and IBC storage

Description

Upgrade to a 60-inch (1524-mm) double door with UL Listed, keyed lockset and gain additional clearance for pallets, IBCs and larger items.

For use on 6- thru 16-drum, 2- and 4-hour fire-rated lockers, the 36-inch (914-mm) right side door serves as a personnel entrance, while the 24-inch (610-mm) left side door opens from the inside for drum loading.

- Large half of door includes door closer and does not stay open on its own.
- This accessory must be purchased in conjunction with a locker to ensure proper installation and/or to retain FM approval.

Specifications

Model No	915702
UPC	697841168336
International Model No.	915702
Color	Bone
Material Specifications	Steel
Dimensions, Exterior	80" H x 60" W
	176mm H x 132mm W
Dimensions, Interior	79" H x 59" W
	174mm H x 130mm W
Number of Doors	2
Door Type	Fire-rated
Door Hinge	24" Left Hinge, 36" Right Hinge
Door Height inch	80
Door Width inch	60
Door Height mm	176
Door Width mm	132
Net Weight, lbs	1.0
Net Weight, kg	1.0